

INSPEX II

simply powerful



Simply Powerful Digital Microscope System

Productivity.



AshCal™

Inspex II is factory calibrated before shipping. No time is wasted performing recalibrations between changing magnifications

Quality.



2D Measurement & Annotation

Point to point measurement and annotation of samples and creation of graticules

Functionality.



On-Screen Digital Graticules

Create Go-No-Go on screen digital graticules to quickly identify sample defects



Save to Network

Networking enables direct saving to the server or cloud for increased workflow efficiency



On Screen Preset Buttons

On Screen Preset Buttons allow quick access to pre-configured part-specific system settings



User Privileges

User privilege settings enables operational control and traceability




Image Stamping

Image stamping with time, date, user and magnification level



Image Stacking

Inspex II automatically captures several images at different focal depths to create an image based on the sharpest regions from each capture



Applications

- In Process Visual Inspection of Component Parts
- Final QC Release Inspection
- Standardisation and Control of Inspection Process
- Documentation of Inspection Process

Industries

- Electronics
- Medical Device Manufacture
- Polymers
- Metalworking
- Automotive